

# Y-140 – S-3 HPB™ Yarn

S-3 HPB<sup>™</sup> yarns are designed for medical applications and have been tested for cytotoxic effects in accordance with ISO 10993-5: Biological Evaluation of Medical Devices, Part 5: Tests for In Vitro Cytotoxicity. The results of that testing showed no evidence of cell lysis or toxicity and so met the requirements of the test since the grade was less than "mild reactivity", Grade 2.

# **General Product Specifications**

Product	SCG37
Glass Type	S-3 HPB
Filament Diameter - µm	9
Binder	383
Bobbin	7636
Plies	1/0
Nominal Yield - yd/lb	3,750
Tex - g/1000 m	132.20
Tex Tolerance +/-	12.00
Nominal Solids - %	0.80
Solids Tolerance +/-	0.20
Nominal Twist - TPI (TPM)	0.5Z (Z20)
Twist Tolerance +/- TPI (TPM)	0.15 (6)
Maximum Broken Filaments*	15
Minimum Tensile** - Ib (N)	21.6 (96.1)

### **Product Information**

\* Broken filaments based on average 360° count

\*\* Average of 5 measurements per bobbin

### **Nominal Product Characteristics**

(For reference only, not specified or controlled)

Average Bare Glass Tensile* - lb	30.0
(N)	(133.4)
Approximate Yarn Diameter - in	0.0156
(mm)	(0.396)

\* Average tensile per bobbin

### **Packaging Information**

Bobbin		7636		
Nominal Bobbin Weight - lb (kg)		2.2 (1.00)		
Minimum Bobbin Weight - Ib (kg)		0.25 (0.11)		
Metered Bobbin Length - yd (m)		8100 (7400)		
Metered Ratio - %		50		
	Rev 7, 10.22.2020			


Product samples available upon request, please contact your AGY representative for details



# Y-140 – S-3 HPB™ Yarn

## Nominal Packaging Dimensions

Bobbin	Pallet	Bobbins / Layer	Layers / Carton	Cartons / Pallet	Bobbins / Pallet	L-in (cm)	W-in (cm)	H-in (cm)		
7636	Wood	18	3	4	216	45.5 (115.6)	45.5 (115.6)	45.5 (115.6)		



## Storage, Shelf Life and Handling

#### Storage and Shelf Life:

AGY recommends storing the materials in accordance with appropriate safety considerations, away from exposure to the elements and at 65-80F (18-27C) and 50-70% humidity. If the materials are stored under these conditions, they are stable, non reactive and will not degrade or exhibit negative characteristics for at least 3 years from the date of manufacture. Unused, unopened product older than this is likely still in good condition, however careful evaluation is recommended. Prior to use, pallets should be placed in the production area and any plastic wrap removed for a minimum of 24 hours to allow the material to acclimate to the processing environment. Special care should be given to pallets being moved from a cold environment into a warm, humid area as condensation may occur and this additional moisture can negatively impact the runability of the material, however, once the material has acclimated, this will no longer be an issue.

For product traceability reasons, the pallet label should be recorded or retained.

#### Handling:

Fiberglass products process best if temperature and humidity are controlled, primarily because this will help to minimize the buildup of static electricity, fuzz and fly. AGY recommends that the material be run at 70 +/- 5 degrees F (18-27C) and 60 +/- 5% RH.

# **Test Methods and Certificates**

A copy of test methods and or a certificate of conformity may be issued upon request.

Packages will be firmly and evenly wound on the bobbin, and free from defects in workmanship. AGY accepts no responsibility for damaged material that shows any signs of physical abuse.

#### For additional product information, refer to PTS M-710

AGY – World Headquarters / Americas 2556 Wagener Road Aiken, South Carolina, USA 29801 Phone: +(1) 888.434.0945 (toll free) +(1) 803.643.1501 Fax: +(1) 803.643.1180 Email: asktheexpert@agy.com AGY – Europe Le Gemellyon Nord 57 Boulevard Marius Vivier Merle 69003 Lyon, France Phone: +(33) 4727 81775 Fax: +(33) 4727 81780

#### www.agy.com